



# model 7601.15

## ASME Portable Air-Pressurized Emergency Eyewash

### FEATURES & BENEFITS

#### CONSTRUCTION

Stainless steel constructed tank makes for a solid portable unit with added resistance against corrosion and breakage.

#### ADDED PROTECTION

Green polyethylene plastic dust covers that release with water pressure keep the unit protected from debris up until the last second before use further optimizing operation.

#### VALVES

Valve comes equipped with stainless steel ball and stem for added protection against corrosion and breakage. Full continuous flow occurs with the simple push of a stainless steel flag.

#### SAFETY

Air pressure gauge, pressure relief valve, and fire-type air fill valve decrease the possibility of mishaps and make for a safer piece of emergency equipment.

#### FLOW CONTROLS

Green ABS plastic soft-flo anti-surge heads distribute water at a rate of .25 gpm (.9 L) when pressure is between 30 and 90 psi (2.1 and 6.2 bar).

#### ANSI COMPLIANCE

10 useable gallons of water provide 15 minute flushing.



### SPECIFICATIONS

Model 7601.15 portable, air pressure operated eyewash shall include an ASME rated stainless steel 15-gallon (56.8 L) tank, ABS plastic anti-surge eyewash heads with integral flow controls and dust covers, chrome-plated brass ball valve equipped with stainless steel ball and stem, air pressure relief valve, and fire-type air fill valve. Unit shall also include label-mounted operating instructions. Additive not included - order separately.

### OPTIONS


- ☐ Water Additive: Model 9082, 'sterile' bacteriostatic preservative for use in portable eyewash stations. One 5 oz. (148 ml) bottle will preserve 5 to 20 gallons (18.9 to 75.7 L) of potable water for up to three months. Four bottles per carton.
- ☐ Emergency Body Spray: Model 8901B, wall-mounted body spray with 8-foot (243.8 cm) pressure rated hose, including wall mounting bracket.
- ☐ Transport Cart: Model 9008 cart designed to transport all stainless steel portable eyewashes.

For more information, visit [www.hawasco.com](http://www.hawasco.com) or call (888) 640-4297.


### APPLICATIONS

Where the eyes of any person may be exposed to injurious or corrosive materials, when suitable facilities for quick flushing of the eyes needs to be provided and a continuous supply of water is not available. Although the 7601.15 may be used in a wide variety of locations, it is ideal for the remote and low traffic areas where protective and mobile measures may still be needed. Emergency eyewash equipment shall be in unobstructed and accessible locations that require no more than 10 seconds for the injured person to reach. Model 7601.15 is certified by CSA to meet the ANSI Z358.1 Standard for Emergency Eyewash and Shower Equipment.





- NOTES:
1. WHEN INSTALLING THIS UNIT, LOCAL , STATE, OR FEDERAL CODES SHOULD BE ADHERED TO FOR INSTALLATION DIMENSIONS (LOCATIONS), WASTE AND SUPPLY REQUIREMENTS OTHER THAN SHOWN.
  2. TO COMPLY WITH ANSI Z358.1-2014 FOR EMERGENCY EYEWASH OR EYE/FACE WASH:  
EYEWASH OR EYE/FACE WASH SHALL BE POSITIONED SUCH THAT FLUSHING FLUID PATTERN IS NOT LESS THAN 33" (838mm) AND NO GREATER THAN 53" (1346mm) FROM SURFACE ON WHICH USER STANDS; AND 6.0" (153mm) MINIMUM FROM WALL OR NEAREST OBSTRUCTION.
  3. EYEWASH HEAD ASSEMBLY MUST BE PARALLEL TO WALL OR OBSTRUCTION TO MEET CRITERIA STATED IN ACCORDANCE WITH NOTES 1 AND 2.
  4. PRESSURIZE TO 100 PSI. REFILL IF PRESSURE BECOMES LESS THAN 95 PSI.
  5. \* DIMENSIONS MAY VARY BY  $\pm 1/2"$  (13 mm).



**Haws®**

1455 KLEPPE LANE  
SPARKS, NEVADA 89431  
(775) 359-4712 FAX (775) 359-7424  
E-MAIL: HAWS@HAWS.CO.COM  
WEBSITE: WWW.HAWS.CO.COM

ECN NO. 5050	REVISED PER ECN: 5239	BY: VWC	MODEL(S)	PART NUMBER
DRAWN: JL	DATE: 05/09/16	CHKD.: VWC	7601.15 15 GAL EYEWASH	0510000133.D
APPROVED: FV	DATE: 11/23/17	SCALE: 1:1	DRAWING TYPE: INSTALLATION	REVISION 4
			SIZE: A	SHEET 1 OF 1